



SPLO 100x30 NBR-55

Suction plate SPLO, available in various diameters and optionally with touch valve, is delivered with support plate vulcanized to elastomer part.


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Dimension (LxW)	100 x 30
Height H	21.00 mm

Design data

Attribute	Value
Height H2	6.00 mm
Height H	21.00 mm
Head length Lk	120.00 mm
Spring stroke Z	5.0 mm
Suction cup width Bs	28.70 mm
Ls	98.00 mm
Lmax.(S)	102.80 mm
Bmax(S)	33.50 mm
Bk	30.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Design data SPLO 100x30 NBR-55

Suction plate (oval)

SPLO 100x30 NBR-55



Art.-Nr.: 10.01.05.00182



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Workpiece radius min. (convex)	25.0 mm
Suction force (-600mbar)	126.00 N
Weight	200.0 g
Dimension (LxW)	100 x 30
Volume	10.015 cm ³
Number of folds	0.0
Product family	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00182



WWW.SCHMALZ.COM/10.01.05.00182