



SPLO 100x30 NBR-55

Çeşitli çaplarda ve isteğe bağlı olarak dokunmatik valfli olarak temin edilebilen vakum plakası SPLO, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	100 x 30
Yükseklik H	21.00 mm

Tasarım verileri

Attribute	Value
Yükseklik H2	6.00 mm
Yükseklik H	21.00 mm
Kafa uzunluğu Lk	120.00 mm
Yay stroku Z	5.0 mm
Vantuz genişliği Bs	28.70 mm
Ls	98.00 mm
Lmaks.(S)	102.80 mm
Bmax(S)	33.50 mm
Bk	30.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPLO 100x30 NBR-55

Art.-Nr.: 10.01.05.00182



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	25.0 mm
Emme kuvveti (-600mbar)	126.00 N
Ağırlık	200.0 g
Boyutlar (LxW)	100 x 30
Cilt	10.015 cm ³
Körük Sayısı	0.0
Ürün ailesi	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00182

