



SPLO 300x55 NBR-55

Çeşitli çaplarda ve isteğe bağlı olarak dokunmatik valfli olarak temin edilebilen vakum plakası SPLO, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	300 x 55
Yükseklik H	19.00 mm

Tasarım verileri

Attribute	Value
Yükseklik H	19.00 mm
Kafa uzunluğu Lk	275.30 mm
Yay stroku Z	6.8 mm
Uzunluk L3	273.00 mm
Genişlik B3	28.00 mm
Vantuz genişliği Bs	51.40 mm
Ls	296.40 mm
Lmaks.(S)	305.00 mm
Bmaks(S)	60.00 mm
Bk	31.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPLO 300x55 NBR-55

Art.-Nr.: 10.01.05.00187



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Emme kuvveti (-600mbar)	710.00 N
Ağırlık	530.0 g
Boyutlar (LxW)	300 x 55
Cilt	92.727 cm ³
Körük Sayısı	0.0
Ürün ailesi	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00187

