



SPLO 300x100 NBR-55 TV

Çeşitli çaplarda ve isteğe bağlı olarak dokunmatik valfli olarak temin edilebilen vakum plakası SPLO, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	300 x 100
Yükseklik H	25.00 mm

Tasarım verileri

Attribute	Value
Uzunluk L2	92.00 mm
Yükseklik H1	53.50 mm
Yükseklik H	25.00 mm
Kafa uzunluğu Lk	266.70 mm
Diş G1	G1/4"-M
Diş uzunluğu LG1	13.0 mm
Diş G2	G1/8"-F
Diş uzunluğu LG2	9.5 mm
Diş uzunluğu LG3	9.0 mm
Yay stroku Z	8.8 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPLO 300x100 NBR-55 TV

Vakum plakası (oval)

SPLO 300x100 NBR-55 TV



Art.-Nr.: 10.01.05.00188



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	175.0 mm
Emme kuvveti (-600mbar)	1250.00 N
Ağırlık	1300.0 g
Boyutlar (LxW)	300 x 100
Cilt	256.392 cm ³
Körük Sayısı	0.0
Ürün ailesi	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00188



WWW.SCHMALZ.COM/10.01.05.00188