

Düz vantuz (oval)

SGO 24x8 NBR-CO-55 N022




Art.-Nr.: 10.01.05.00227



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyutlar (LxW)	24x8

SGO 24x8 NBR-CO-55 N022



Tasarım verileri

Attribute	Value
Yükseklik H2	3,00 mm
Yükseklik H	12,00 mm
Kafa çapı Dk	11,5 mm
Nominal çap dn	1,50 mm
İç çap d1	7,0 mm
İç çap d	5,50 mm
Yay stroku Z	1,0 mm
Yükseklik H3	5,50 mm
Vantuz genişliği Bs	7,60 mm
Ls	23,60 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 24x8 NBR-CO-55 N022



WWW.SCHMALZ.COM/10.01.05.00227

Düz vantuz (oval)

SGO 24x8 NBR-CO-55 N022



Art.-Nr.: 10.01.05.00227



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Emme kuvveti (-600mbar)	8,00 N
Ağırlık	1,0 g
Ürün ailesi	SGO
Boyutlar (LxW)	24x8

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00227



Sipariş Verisi Aksesuarlar 10.01.05.00227

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N022 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N022 G1/8-IG DN350



WWW.SCHMALZ.COM/10.01.05.00227