

Düz vantuz (oval)

SGO 12x4 NBR-55 N020




Art.-Nr.: 10.01.05.00235



SGO 12x4 NBR-55 N020

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	12 x 4



Tasarım verileri SGO 12x4 NBR-55 N020

Tasarım verileri

Attribute	Value
Yükseklik H2	9.30 mm
Yükseklik H	15.00 mm
Kafa çapı Dk	8.0 mm
Nominal çap dn	1.50 mm
İç çap d	4.20 mm
Yay stroku Z	0.5 mm
Vantuz genişliği Bs	4.00 mm
Ls	12.00 mm
Lmaks.(S)	13.00 mm
Bmax(S)	5.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.05.00235

Düz vantuz (oval)

SGO 12x4 NBR-55 N020



Art.-Nr.: 10.01.05.00235



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	1.80 N
Ağırlık	0.5 g
Boyutlar (LxW)	12 x 4
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00235



Veri aksesuarları sipariş edin 10.01.05.00235

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N020 M5-AG DN180
	10.01.01.00312



WWW.SCHMALZ.COM/10.01.05.00235