



Technical data


Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Connection	G 1/4" -M
Dimension (LxW)	60x20
Nipple material	Aluminum
Material property	non-marking

SGON 60x20 HT1-60 G1/4-AG

Suction cup SGON (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type SGO – elastomer part, available in various dimensions (LxW) and materials
- Connection nipple of type SA-NIP – available with various threads
- Cups of the size 24 x 8 mm and larger are delivered with a two-ear clamp

Available spare parts: suction cup SGO, connection nipple SA-NIP, two-ear clamp



Design data

Height H	26.00 mm
Nominal diameter dn	3.50 mm
Thread G1	G 1/4" -M
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	2.5 mm
Suction cup width Bs	19.00 mm
Ls	59.00 mm
Lmax.(S)	61.00 mm
Bmax(S)	22.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Design data SGON 60x20 HT1-60 G1/4-AG

Flat suction cup (oval)

SGON 60x20 HT1-60 G1/4-AG



Art.-Nr.: 10.01.05.00412



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	20.0 mm
Suction force (-600mbar)	50.10 N
Weight	19.00 g
Volume	3.611 cm ³
Number of folds	0.0
Product family	SGON
Dimension (LxW)	60x20

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.05.00412

Typ		Item number
Suction cup connection nipple	SA-NIP N023 G1/4-AG DN350	10.01.05.00122
Suction cup connection nipple	SA-NIP N023 G1/4-IG DN350	10.01.05.00121
Two-ear clamp	ZOKL 15-18	10.07.10.00033



Ordering Data Wear Parts 10.01.05.00412

Typ		Item number
Flat suction cup (oval)	SGO 60x20 HT1-60 N023	10.01.05.00440
Two-ear clamp	ZOKL 15-18	10.07.10.00033



WWW.SCHMALZ.COM/10.01.05.00412