

Flat suction cup (oval)

SGO 60x20 HT1-60 N023


Art.-Nr.: 10.01.05.00440



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Dimension (LxW)	60x20
Material property	non-marking

SGO 60x20 HT1-60 N023



Design data

Height H2	8.00 mm
Height H	21.00 mm
Head diameter Dk	15.5 mm
Nominal diameter dn	4.00 mm
Internal diameter d1	13.0 mm
Internal diameter d	11.50 mm
Spring stroke Z	2.5 mm
Height H3	10.00 mm
Suction cup width Bs	19.00 mm
Ls	59.00 mm
Lmax.(S)	61.00 mm
Bmax(S)	22.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SGO 60x20 HT1-60 N023



WWW.SCHMALZ.COM/10.01.05.00440

1

Flat suction cup (oval)

SGO 60x20 HT1-60 N023



Art.-Nr.: 10.01.05.00440



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Suction force (-600mbar)	50.10 N
Weight	6.40 g
Product family	SGO
Dimension (LxW)	60x20

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Accessories 10.01.05.00440

Typ		Item number
Suction cup connection nipple	SA-NIP N023 G1/4-AG DN350	10.01.05.00122
Suction cup connection nipple	SA-NIP N023 G1/4-IG DN350	10.01.05.00121



WWW.SCHMALZ.COM/10.01.05.00440