




SGO 75x25 HT1-60 N023



Tasarım verileri SGO 75x25 HT1-60 N023

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyutlar (LxW)	75 x 25
Malzeme özelliği	iz bırakmayan

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	21.00 mm
Kafa çapı Dk	17.5 mm
Nominal çap dn	4.00 mm
İç çap d1	13.0 mm
İç çap d	11.50 mm
Yay stroku Z	2.8 mm
Yükseklik H3	10.00 mm
Vantuz genişliği Bs	24.00 mm
Ls	74.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Düz vantuz (oval)

SGO 75x25 HT1-60 N023



Art.-Nr.: 10.01.05.00441



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Emme kuvveti (-600mbar)	78.30 N
Ağırlık	17.8 g
Boyutlar (LxW)	75 x 25
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00441



Veri aksesuarları sipariş edin 10.01.05.00441

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N023 G1/4-AG DN350 10.01.05.00122
Vantuz bağlantı nipel	SA-NIP N023 G1/4-IG DN350 10.01.05.00121



WWW.SCHMALZ.COM/10.01.05.00441