

Düz vantuz (oval)

SGO 4x2 NBR-ESD-55 N003

Art.-Nr.: 10.01.05.00937



SGO 4x2 NBR-ESD-55 N003


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A

Tasarım verileri

Attribute	Value
Yükseklik H2	1.50 mm
Yükseklik H	6.00 mm
Kafa çapı Dk	6.0 mm
Nominal çap dn	1.20 mm
İç çap d	1.50 mm
Yay stroku Z	0.5 mm
Vantuz genişliği Bs	2.00 mm
Ls	4.00 mm
Lmaks.(S)	4.50 mm
Bmax(S)	2.50 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SGO 4x2 NBR-ESD-55 N003



WWW.SCHMALZ.COM/10.01.05.00937

Düz vantuz (oval)

SGO 4x2 NBR-ESD-55 N003



Art.-Nr.: 10.01.05.00937



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	0.40 N
Ağırlık	0.1 g
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00937



WWW.SCHMALZ.COM/10.01.05.00937