

Flat suction cup (oval)

SGO 24x8 SI-HD-65 N022


Art.-Nr.: 10.01.05.01036



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65.0 Shore A

SGO 24x8 SI-HD-65 N022



Tasarım verileri

Attribute	Value
Yükseklik H2	3.00 mm
Yükseklik H	12.00 mm
Kafa çapı Dk	11.5 mm
Nominal çap dn	1.50 mm
İç çap d1	7.0 mm
İç çap d	5.50 mm
Yay stroku Z	1.0 mm
Yükseklik H3	5.50 mm
Vantuz genişliği Bs	7.60 mm
Ls	23.60 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 24x8 SI-HD-65 N022



WWW.SCHMALZ.COM/10.01.05.01036

Flat suction cup (oval)

SGO 24x8 SI-HD-65 N022



Art.-Nr.: 10.01.05.01036



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65.0 Shore A
Emme kuvveti (-600mbar)	8.00 N
Ağırlık	2.6 g
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.01036



Veri aksesuarları sipariş edin 10.01.05.01036

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N022 G1/8-AG DN350 10.01.05.00124
Vantuz bağlantı nipel	SA-NIP N022 G1/8-IG DN350 10.01.05.00123



WWW.SCHMALZ.COM/10.01.05.01036