

Flat suction cup (oval)

SGO 45x15 SI-HD-65 N023


Art.-Nr.: 10.01.05.01038



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65.0 Shore A

SGO 45x15 SI-HD-65 N023



Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	21.00 mm
Kafa çapı Dk	15.5 mm
Nominal çap dn	3.00 mm
İç çap d1	13.0 mm
İç çap d	11.50 mm
Yay stroku Z	2.0 mm
Yükseklik H3	10.00 mm
Vantuz genişliği Bs	14.40 mm
Ls	44.40 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 45x15 SI-HD-65 N023



WWW.SCHMALZ.COM/10.01.05.01038

Flat suction cup (oval)

SGO 45x15 SI-HD-65 N023



Art.-Nr.: 10.01.05.01038



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliđi [Shore A]	65.0 Shore A
Emme kuvveti (-600mbar)	28.20 N
Ağırlık	6.4 g
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.01038



Veri aksesuarları sipariş edin 10.01.05.01038

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N023 G1/4-AG DN350 10.01.05.00122
Vantuz bağlantı nipel	SA-NIP N023 G1/4-IG DN350 10.01.05.00121



WWW.SCHMALZ.COM/10.01.05.01038