

Flat suction cup (oval)

SGO 75x25 SI-HD-65 N023


Art.-Nr.: 10.01.05.01040



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65.0 Shore A

SGO 75x25 SI-HD-65 N023



Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	21.00 mm
Kafa çapı Dk	17.5 mm
Nominal çap dn	4.00 mm
İç çap d1	13.0 mm
İç çap d	11.50 mm
Yay stroku Z	2.8 mm
Yükseklik H3	10.00 mm
Vantuz genişliği Bs	24.00 mm
Ls	74.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 75x25 SI-HD-65 N023



WWW.SCHMALZ.COM/10.01.05.01040

Flat suction cup (oval)

SGO 75x25 SI-HD-65 N023



Art.-Nr.: 10.01.05.01040



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliđi [Shore A]	65.0 Shore A
Emme kuvveti (-600mbar)	78.30 N
Ağırlık	17.9 g
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.01040



Veri aksesuarları sipariş edin 10.01.05.01040

Typ	Ürün numarası
Vantuz bağlantı nipelı	SA-NIP N023 G1/4-AG DN350
Vantuz bağlantı nipelı	SA-NIP N023 G1/4-IG DN350



WWW.SCHMALZ.COM/10.01.05.01040