

Flat suction cup (oval)

## SGO 90x30 SI-HD-65 N023




Art.-Nr.: 10.01.05.01041



### Technical data

Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Dimension (LxW)	90x30

SGO 90x30 SI-HD-65 N023



### Design data

Height H2	8.00 mm
Height H	21.00 mm
Head diameter Dk	17.5 mm
Nominal diameter dn	4.00 mm
Internal diameter d1	13.0 mm
Internal diameter d	11.50 mm
Spring stroke Z	3.5 mm
Height H3	10.00 mm
Suction cup width Bs	29.00 mm
Ls	89.00 mm
Lmax.(S)	92.50 mm
Bmax(S)	33.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SGO 90x30 SI-HD-65 N023



[WWW.SCHMALZ.COM/10.01.05.01041](http://WWW.SCHMALZ.COM/10.01.05.01041)

Flat suction cup (oval)

## SGO 90x30 SI-HD-65 N023



Art.-Nr.: 10.01.05.01041



### Technical data

Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Suction force (-600mbar)	112.60 N
Weight	25.70 g
Product family	SGO
Dimension (LxW)	90x30

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Ordering Data Accessories 10.01.05.01041

Typ		Item number
Suction cup connection nipple	SA-NIP N023 G1/4-AG DN350	10.01.05.00122
Suction cup connection nipple	SA-NIP N023 G1/4-IG DN350	10.01.05.00121



[WWW.SCHMALZ.COM/10.01.05.01041](http://WWW.SCHMALZ.COM/10.01.05.01041)