



FGB 25 SI-55 N049


Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	25.00
Körük Sayısı	3.5

Tasarım verileri

Attribute	Value
Yükseklik H2	9.00 mm
Yükseklik H	43.00 mm
Dış çap D1	25.0 mm
Kafa çapı Dk	10.0 mm
d2	10.0 mm
İç çap d	5.00 mm
Yay stroku Z	22.0 mm
Çap Ds	23.0 mm
Çap Dmax(S)	26.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGB 25 SI-55 N049

Art.-Nr.: 10.01.06.00108



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
İş parçası yarıçapı dak (dışbükey)	25.0 mm
Çekme kuvveti	20.00 N
Emme kuvveti (-600mbar)	4.50 N
Ağırlık	5.5 g
Cilt	7.071 cm ³
Boyut	25.00
Körük Sayısı	3.5
Ürün ailesi	FGB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00108



WWW.SCHMALZ.COM/10.01.06.00108