




FGA 110 SI-55 N010

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	110.00
Körük Sayısı	1.5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FGA 110 SI-55 N010

Tasarım verileri

Attribute	Value
Yükseklik H	55.00 mm
Dış çap D1	123.0 mm
Kafa çapı Dk	86.0 mm
d2	80.0 mm
İç çap d	7.00 mm
Dmk	40.0 mm
Yay stroku Z	29.5 mm
Çap Ds	111.0 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	130.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Körüklü vantuz (yuvarlak)

FGA 110 SI-55 N010



Art.-Nr.: 10.01.06.00115



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	85.0 mm
Emme kuvveti (-600mbar)	280.00 N
Ağırlık	263.5 g
Boyut	110.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00115



Veri aksesuarları sipariş edin 10.01.06.00115

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N010 G1/2-IG
	10.01.01.00796



WWW.SCHMALZ.COM/10.01.06.00115