

Körüklü vantuz (yuvarlak)

FGA 150 NBR-70 N010



Art.-Nr.: 10.01.06.00116



FGA 150 NBR-70 N010


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	70.0 Shore A
Boyut	150.00
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Yükseklik H	74.00 mm
Dış çap D1	168.0 mm
Kafa çapı Dk	120.0 mm
d2	111.0 mm
İç çap d	7.00 mm
Dmk	40.0 mm
Yay stroku Z	37.0 mm
Çap Ds	150.0 mm
Yükseklik H4	10.00 mm
Çap Dmax(S)	177.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 150 NBR-70 N010



WWW.SCHMALZ.COM/10.01.06.00116

Körüklü vantuz (yuvarlak)

FGA 150 NBR-70 N010



Art.-Nr.: 10.01.06.00116



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	70.0 Shore A
İş parçası yarıçapı dak (dışbükey)	250.0 mm
Emme kuvveti (-600mbar)	570.00 N
Ağırlık	802.8 g
Boyut	150.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00116



Veri aksesuarları sipariş edin 10.01.06.00116

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N010 G1/2-IG
	10.01.01.00796



WWW.SCHMALZ.COM/10.01.06.00116