

Körüklü vantuz (yuvarlak)

FGA 43 NBR-55 N018



Art.-Nr.: 10.01.06.00131



FGA 43 NBR-55 N018


Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	43,00
Körük Sayısı	1,5

Tasarım verileri

Yükseklik H2	13,00 mm
Yükseklik H	27,60 mm
Dış çap D1	45,9 mm
Kafa çapı Dk	18,0 mm
İç çap d1	14,5 mm
d2	21,9 mm
İç çap d	8,00 mm
Yay stroku Z	10,0 mm
Çap Ds	38,0 mm
Yükseklik H3	17,10 mm
Çap Dmax(S)	47,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 43 NBR-55 N018



WWW.SCHMALZ.COM/10.01.06.00131

Körüklü vantuz (yuvarlak)

FGA 43 NBR-55 N018



Art.-Nr.: 10.01.06.00131



Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	60,0 mm
Emme kuvveti (-600mbar)	22,80 N
Ağırlık	11,00 g
Boyut	43,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.06.00131

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440



WWW.SCHMALZ.COM/10.01.06.00131