

Bellows suction cup (round)

FGA 43 NBR-55 N018




Art.-Nr.: 10.01.06.00131



Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	43.00
Number of folds	1.5

FGA 43 NBR-55 N018



Design data

Height H2	13.00 mm
Height H	27.60 mm
Outside diameter D1	45.9 mm
Head diameter Dk	18.0 mm
Internal diameter d1	14.5 mm
d2	21.9 mm
Internal diameter d	8.00 mm
Spring stroke Z	10.0 mm
Diameter Ds	38.0 mm
Height H3	17.10 mm
Diameter Dmax(S)	47.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FGA 43 NBR-55 N018



WWW.SCHMALZ.COM/10.01.06.00131

1

Art.-Nr.: 10.01.06.00131

**Technical data**

Suction cup material	Nitrile rubber NBR
Workpiece radius min. (convex)	60.0 mm
Suction force (-600mbar)	22.80 N
Weight	11.00 g
Size	43.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.00131**

Typ		Item number
Suction cup connection nipple	SA-NIP N018 G1/4-AG DN440	10.01.06.01065
Suction cup connection nipple	SA-NIP N018 G1/4-IG DN440	10.01.06.01066

