




FG 62 NBR-55 N018

Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	62,00
Körük Sayısı	2,5



Tasarım verileri FG 62 NBR-55 N018

Tasarım verileri

Yükseklik H2	13,00 mm
Yükseklik H	54,00 mm
Dış çap D1	62,0 mm
Kafa çapı Dk	18,0 mm
d2	29,5 mm
İç çap d	8,00 mm
Yay stroku Z	29,0 mm
Çap Ds	62,2 mm
Çap Dmax(S)	65,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00142

**Teknik veriler**

Meme ucu ailesi	N 018
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Çekme kuvveti	137,00 N
Emme kuvveti (-600mbar)	41,01 N
Ağırlık	39,20 g
Cilt	61,122 cm ³
Boyut	62,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Sipariş Verisi Aksesuarlar 10.01.06.00142**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N018 G1/4-AG DN440 10.01.06.01065
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440 10.01.06.01066

