




FG 32 SI-55 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	32,00
Körük Sayısı	2,5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FG 32 SI-55 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	13,00 mm
Yükseklik H	37,50 mm
Dış çap D1	32,4 mm
Kafa çapı Dk	18,0 mm
İç çap d1	15,0 mm
d2	16,0 mm
İç çap d	8,00 mm
Yay stroku Z	15,0 mm
Çap Ds	32,0 mm
Yükseklik H3	17,00 mm
Çap Dmax(S)	33,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00144

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 018
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	35,0 mm
Çekme kuvveti	36,90 N
Emme kuvveti (-600mbar)	12,06 N
Ağırlık	8,90 g
Cilt	9,768 cm ³
Boyut	32,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00144

**Sipariş Verisi Aksesuarlar 10.01.06.00144**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N018 G1/4-AG DN440 10.01.06.01065
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440 10.01.06.01066

