




FG 88 SI-55 N019

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	88.00
Körük Sayısı	2.5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FG 88 SI-55 N019

Tasarım verileri

Attribute	Value
Yükseklik H2	19.70 mm
Yükseklik H	86.50 mm
Dış çap D1	88.2 mm
Kafa çapı Dk	24.7 mm
İç çap d1	25.0 mm
d2	29.3 mm
İç çap d	11.70 mm
Yay stroku Z	34.0 mm
Çap Ds	89.0 mm
Yükseklik H3	26.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00147

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 019
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	100.0 mm
Çekme kuvveti	286.00 N
Emme kuvveti (-600mbar)	40.46 N
Ağırlık	158.5 g
Cilt	143.668 cm ³
Boyut	88.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00147

**Veri aksesuarları sipariş edin 10.01.06.00147**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N019 G1/4-AG DN820
Vantuz bağlantı nipel	SA-NIP N019 G1/4-IG DN820

