




FG 30 VU1-72 N013

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	30.00
Körük Sayısı	2.5



Tasarım verileri FG 30 VU1-72 N013

Tasarım verileri

Attribute	Value
Yükseklik H2	12.00 mm
Yükseklik H	40.00 mm
Dış çap D1	30.0 mm
Kafa çapı Dk	18.0 mm
İç çap d1	15.0 mm
d2	15.0 mm
İç çap d	8.00 mm
Yay stroku Z	15.0 mm
Çap Ds	29.0 mm
Yükseklik H3	16.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00173

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 013
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
İş parçası yarıçapı dak (dışbükey)	15.0 mm
Çekme kuvveti	32.00 N
Emme kuvveti (-600mbar)	13.50 N
Ağırlık	8.6 g
Cilt	10.095 cm ³
Boyut	30.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00173

**Veri aksesuarları sipariş edin 10.01.06.00173**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N013 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N013 G1/4-IG DN350

WWW.SCHMALZ.COM/10.01.06.00173