



FG 60 VU1-72 N014


Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	60.00
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Yükseklik H2	12.00 mm
Yükseklik H	55.00 mm
Dış çap D1	60.0 mm
Kafa çapı Dk	21.0 mm
İç çap d1	20.0 mm
d2	36.0 mm
İç çap d	12.00 mm
Yay stroku Z	30.0 mm
Çap Ds	59.0 mm
Yükseklik H3	18.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 60 VU1-72 N014

Art.-Nr.: 10.01.06.00174

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 014
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Çekme kuvveti	100.00 N
Emme kuvveti (-600mbar)	61.00 N
Ağırlık	36.6 g
Cilt	68.277 cm ³
Boyut	60.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00174

**Veri aksesuarları sipariş edin 10.01.06.00174**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N014 G1/4-AG DN600
Vantuz bağlantı nipel	SA-NIP N014 G1/4-IG DN600

