



FGA 30 VU1-72 N013


Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	30.00
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Yükseklik H2	12.00 mm
Yükseklik H	27.00 mm
Dış çap D1	30.0 mm
Kafa çapı Dk	18.0 mm
İç çap d1	15.0 mm
d2	17.0 mm
İç çap d	8.00 mm
Yay stroku Z	8.5 mm
Çap Ds	29.0 mm
Yükseklik H3	16.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 30 VU1-72 N013

Art.-Nr.: 10.01.06.00177



Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Çekme kuvveti	32.00 N
Emme kuvveti (-600mbar)	13.50 N
Ağırlık	6.5 g
Cilt	5.756 cm ³
Boyut	30.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00177



Veri aksesuarları sipariş edin 10.01.06.00177

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N013 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N013 G1/4-IG DN350

