


FGA 85 VU1-72 N015 ON

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	85.00
Körük Sayısı	1.5



Tasarım verileri FGA 85 VU1-72 N015 ON

Tasarım verileri

Attribute	Value
Yükseklik H2	20.00 mm
Yükseklik H	47.00 mm
Dış çap D1	85.5 mm
Kafa çapı Dk	25.0 mm
İç çap d1	25.0 mm
d2	50.2 mm
İç çap d	12.00 mm
Yay stroku Z	15.0 mm
Çap Ds	82.5 mm
Yükseklik H3	25.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00190

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
İş parçası yarıçapı dak (dışbükey)	80.0 mm
Çekme kuvveti	250.00 N
Emme kuvveti (-600mbar)	140.00 N
Ağırlık	95.0 g
Cilt	75.897 cm ³
Boyut	85.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00190

**Veri aksesuarları sipariş edin 10.01.06.00190**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N015 G1/4-AG DN600
Vantuz bağlantı nipel	SA-NIP N015 G1/4-IG DN600

WWW.SCHMALZ.COM/10.01.06.00190