




FGA 60 VU1-72 N014 ON

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	60.00
Körük Sayısı	1.5



Tasarım verileri FGA 60 VU1-72 N014 ON

Tasarım verileri

Attribute	Value
Yükseklik H2	12.00 mm
Yükseklik H	34.00 mm
Dış çap D1	60.0 mm
Kafa çapı Dk	21.0 mm
İç çap d1	20.0 mm
d2	40.0 mm
İç çap d	12.00 mm
Yay stroku Z	12.0 mm
Çap Ds	57.0 mm
Yükseklik H3	22.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00207



Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Çekme kuvveti	120.00 N
Emme kuvveti (-600mbar)	75.00 N
Ağırlık	29.2 g
Cilt	34.270 cm ³
Boyut	60.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00207



Veri aksesuarları sipariş edin 10.01.06.00207

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N014 G1/4-AG DN600
Vantuz bağlantı nipel	SA-NIP N014 G1/4-IG DN600

