


FG 85 VU1-72 N015 ON

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	85.00
Körük Sayısı	2.5



Tasarım verileri FG 85 VU1-72 N015 ON

Tasarım verileri

Attribute	Value
Yükseklik H2	20.00 mm
Yükseklik H	85.00 mm
Dış çap D1	85.0 mm
Kafa çapı Dk	25.0 mm
İç çap d1	25.0 mm
d2	51.0 mm
İç çap d	12.00 mm
Yay stroku Z	45.5 mm
Çap Ds	80.2 mm
Yükseklik H3	27.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00209

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 015
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
İş parçası yarıçapı dak (dışbükey)	60.0 mm
Çekme kuvveti	250.00 N
Emme kuvveti (-600mbar)	120.00 N
Ağırlık	130.0 g
Cilt	201.577 cm ³
Boyut	85.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00209

**Veri aksesuarları sipariş edin 10.01.06.00209**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N015 G1/4-AG DN600
Vantuz bağlantı nipel	SA-NIP N015 G1/4-IG DN600

WWW.SCHMALZ.COM/10.01.06.00209