



FGA 40 VU1-72 N011 ON


Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	40.00
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	27.00 mm
Dış çap D1	40.0 mm
Kafa çapı Dk	14.0 mm
İç çap d1	13.6 mm
d2	26.8 mm
İç çap d	8.00 mm
Yay stroku Z	12.8 mm
Çap Ds	38.0 mm
Yükseklik H3	15.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 40 VU1-72 N011 ON

Art.-Nr.: 10.01.06.00301

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Çekme kuvveti	56.00 N
Emme kuvveti (-600mbar)	33.00 N
Ağırlık	9.0 g
Cilt	12.888 cm ³
Boyut	40.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00301

**Veri aksesuarları sipariş edin 10.01.06.00301**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N011 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N011 G1/4-IG DN350

WWW.SCHMALZ.COM/10.01.06.00301