




FGA 50 VU1-72 N011 ON

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	50.00
Körük Sayısı	1.5



Tasarım verileri FGA 50 VU1-72 N011 ON

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	32.50 mm
Dış çap D1	50.0 mm
Kafa çapı Dk	17.5 mm
İç çap d1	13.6 mm
d2	33.5 mm
İç çap d	8.00 mm
Yay stroku Z	14.5 mm
Çap Ds	47.0 mm
Yükseklik H3	17.80 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Körüklü vantuz (yuvarlak)

FGA 50 VU1-72 N011 ON



Art.-Nr.: 10.01.06.00302



Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Çekme kuvveti	88.00 N
Emme kuvveti (-600mbar)	53.00 N
Ağırlık	18.1 g
Cilt	24.151 cm ³
Boyut	50.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00302



Veri aksesuarları sipariş edin 10.01.06.00302

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N011 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N011 G1/4-IG DN350



WWW.SCHMALZ.COM/10.01.06.00302