

Bellows suction cups (round)

FSG 62 NK-45 G1/4-AG



Art.-Nr.: 10.01.06.00449



Technical data


Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	62.00
Number of folds	2.5
Connection	G1/4"-M
Vacuum connection	G1/4"-M
Nipple material	Aluminum

FSG 62 NK-45 G1/4-AG

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP



Design data

Attribute	Value
Height H	58.00 mm
Nominal diameter dn	4.40 mm
d2	29.5 mm
Thread G1	G1/4"-M
Thread length LG1	11.0 mm
Key width SW1	17.0 mm
Spring stroke Z	29.0 mm
Diameter Ds	62.2 mm
Diameter Dmax(S)	65.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSG 62 NK-45 G1/4-AG



WWW.SCHMALZ.COM/10.01.06.00449

Bellows suction cups (round)

FSG 62 NK-45 G1/4-AG



Art.-Nr.: 10.01.06.00449



Technical data

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	75.0 mm
Pull-off force	137.00 N
Suction force (-600mbar)	41.01 N
Weight	60.0 g
Volume	61.122 cm ³
Size	62.00
Number of folds	2.5
Product family	FSG
Connection	G1/4-AG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00449



Ordering Data Accessories 10.01.06.00449

Typ		Item number
Sealing ring	DR 62/42x5 MOS SI-15	10.01.06.02617
Suction cup cover	SU 70	10.01.01.12838



Ordering Data Spare Parts 10.01.06.00449

Typ		Item number
Suction cup connection nipple	SA-NIP N018 G1/4-AG DN440	10.01.06.01065



Ordering Data Wear Parts 10.01.06.00449

Typ		Item number
Bellows suction cup (round)	FG 62 NK-45 N018	10.01.06.00459



WWW.SCHMALZ.COM/10.01.06.00449