



FG 14 NK-45 N016


Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	14,00
Körük Sayısı	2,5

Tasarım verileri

Attribute	Value
Yükseklik H2	3,80 mm
Yükseklik H	22,80 mm
Dış çap D1	13,9 mm
Kafa çapı Dk	10,0 mm
d2	5,4 mm
İç çap d	4,50 mm
Yay stroku Z	9,0 mm
Çap Ds	14,5 mm
Yükseklik H3	9,00 mm
Çap Dmax(S)	15,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 14 NK-45 N016

Art.-Nr.: 10.01.06.00453

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
İş parçası yarıçapı dak (dışbükey)	15,0 mm
Çekme kuvveti	5,70 N
Emme kuvveti (-600mbar)	1,37 N
Ağırlık	1,50 g
Cilt	1,058 cm ³
Boyut	14,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00453

**Sipariş Verisi Aksesuarlar 10.01.06.00453**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350
Vantuz bağlantı nipel	SA-NIP N016 M5-AG DN250

