



FG 25 NK-45 N016


Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	25.00
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Yükseklik H2	3.80 mm
Yükseklik H	34.00 mm
Dış çap D1	25.0 mm
Kafa çapı Dk	10.0 mm
d2	10.0 mm
İç çap d	4.50 mm
Yay stroku Z	18.0 mm
Çap Ds	23.0 mm
Yükseklik H3	9.00 mm
Çap Dmax(S)	26.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 25 NK-45 N016

Art.-Nr.: 10.01.06.00456

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
İş parçası yarıçapı dak (dışbükey)	30.0 mm
Çekme kuvveti	19.00 N
Emme kuvveti (-600mbar)	4.71 N
Ağırlık	3.6 g
Cilt	5.222 cm ³
Boyut	25.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00456

**Veri aksesuarları sipariş edin 10.01.06.00456**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350 10.01.06.05735
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350 10.01.06.05731

WWW.SCHMALZ.COM/10.01.06.00456