




FG 42 NK-45 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	42.00
Körük Sayısı	2.5



Tasarım verileri FG 42 NK-45 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	13.00 mm
Yükseklik H	46.00 mm
Dış çap D1	43.5 mm
Kafa çapı Dk	18.0 mm
İç çap d1	15.0 mm
d2	17.8 mm
İç çap d	8.00 mm
Yay stroku Z	20.0 mm
Çap Ds	42.6 mm
Yükseklik H3	17.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00458

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 018
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Çekme kuvveti	44.00 N
Emme kuvveti (-600mbar)	14.93 N
Ağırlık	18.0 g
Cilt	19.786 cm ³
Boyut	42.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00458

**Veri aksesuarları sipariş edin 10.01.06.00458**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440

WWW.SCHMALZ.COM/10.01.06.00458