



FG 88 NK-45 N019


Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	88,00
Körük Sayısı	2,5

Tasarım verileri

Attribute	Value
Yükseklik H2	19,70 mm
Yükseklik H	86,50 mm
Dış çap D1	88,2 mm
Kafa çapı Dk	24,7 mm
İç çap d1	25,0 mm
d2	29,3 mm
İç çap d	11,70 mm
Yay stroku Z	34,0 mm
Çap Ds	89,0 mm
Yükseklik H3	26,00 mm
Çap Dmax(S)	95,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 88 NK-45 N019

Art.-Nr.: 10.01.06.00460

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 019
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
İş parçası yarıçapı dak (dışbükey)	100,0 mm
Çekme kuvveti	286,00 N
Emme kuvveti (-600mbar)	40,46 N
Ağırlık	146,50 g
Cilt	143,668 cm ³
Boyut	88,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00460

**Sipariş Verisi Aksesuarlar 10.01.06.00460**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N019 G1/4-AG DN820
Vantuz bağlantı nipel	SA-NIP N019 G1/4-IG DN820

