


Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72,0 Shore A
Boyut	110,00
Körük Sayısı	1,5

FGA 110 VU1-72 N037 ON



Tasarım verileri

Attribute	Value
Yükseklik H	56,00 mm
Dış çap D1	120,0 mm
Kafa çapı Dk	85,0 mm
d2	80,0 mm
İç çap d	5,50 mm
Dmk	55,0 mm
Yay stroku Z	30,0 mm
Çap Ds	110,0 mm
Yükseklik H4	10,00 mm
Çap Dmax(S)	127,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri FGA 110 VU1-72 N037 ON

Körüklü vantuz (yuvarlak)

FGA 110 VU1-72 N037 ON



Art.-Nr.: 10.01.06.00492



Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
İş parçası yarıçapı dak (dışbükey)	100,0 mm
Çekme kuvveti	420,00 N
Emme kuvveti (-600mbar)	295,00 N
Ağırlık	151,30 g
Cilt	328,000 cm ³
Boyut	110,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00492



Sipariş Verisi Aksesuarlar 10.01.06.00492

Typ	Ürün numarası
Vantuz bağlantı disk	SA-SCHE 77 G1/2-IG FSGA
	10.01.06.00593



WWW.SCHMALZ.COM/10.01.06.00492