



FGAO 95x40 VU1-72 N038


Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyutlar (LxW)	95 x 40
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Uzunluk L1	93.00 mm
Genişlik B1	38.00 mm
Yükseklik H	23.50 mm
İç çap d1	7.5 mm
İç çap d	11.50 mm
Yay stroku Z	12.0 mm
Delik aralığı X1	55.0 mm
Vantuz genişliği Bs	40.00 mm
Ls	95.00 mm
Lmaks.(S)	97.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGAO 95x40 VU1-72 N038

Körüklü vantuz (oval)

FGAO 95x40 VU1-72 N038



Art.-Nr.: 10.01.06.00499



Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Çekme kuvveti	110.00 N
Emme kuvveti (-600mbar)	95.00 N
Ağırlık	20.9 g
Boyutlar (LxW)	95 x 40
Körük Sayısı	1.5
Ürün ailesi	FGAO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00499



WWW.SCHMALZ.COM/10.01.06.00499