



FG 12 NBR-55 N016


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	12.00
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Yükseklik H2	3.80 mm
Yükseklik H	21.00 mm
Dış çap D1	12.0 mm
Kafa çapı Dk	10.0 mm
d2	5.0 mm
İç çap d	4.50 mm
Yay stroku Z	7.0 mm
Çap Ds	12.0 mm
Yükseklik H3	9.00 mm
Çap Dmax(S)	13.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 12 NBR-55 N016

Art.-Nr.: 10.01.06.00557

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Çekme kuvveti	3.50 N
Emme kuvveti (-600mbar)	1.18 N
Ağırlık	1.1 g
Cilt	0.747 cm ³
Boyut	12.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00557

**Veri aksesuarları sipariş edin 10.01.06.00557**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350
Vantuz bağlantı nipel	SA-NIP N016 M5-AG DN250

WWW.SCHMALZ.COM/10.01.06.00557