

Bellows suction cup (round)

FG 52 NBR-55 N018




Art.-Nr.: 10.01.06.00583



Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	52.00
Number of folds	2.5

FG 52 NBR-55 N018



Design data

Height H2	13.00 mm
Height H	48.70 mm
Outside diameter D1	52.0 mm
Head diameter Dk	18.0 mm
d2	24.6 mm
Internal diameter d	8.00 mm
Spring stroke Z	25.0 mm
Diameter Ds	52.5 mm
Diameter Dmax(S)	55.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 52 NBR-55 N018



WWW.SCHMALZ.COM/10.01.06.00583

Art.-Nr.: 10.01.06.00583

**Technical data**

Nipple family	N 018
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	75.0 mm
Pull-off force	96.00 N
Suction force (-600mbar)	28.52 N
Weight	24.40 g
Volume	37.587 cm ³
Size	52.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.00583**

Typ		Item number
Suction cup connection nipple	SA-NIP N018 G1/4-AG DN440	10.01.06.01065
Suction cup connection nipple	SA-NIP N018 G1/4-IG DN440	10.01.06.01066

