




FG 52 SI-55 N018

Teknik veriler

Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	52,00
Körük Sayısı	2,5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FG 52 SI-55 N018

Tasarım verileri

Yükseklik H2	13,00 mm
Yükseklik H	48,70 mm
Dış çap D1	52,0 mm
Kafa çapı Dk	18,0 mm
d2	24,6 mm
İç çap d	8,00 mm
Yay stroku Z	25,0 mm
Çap Ds	52,5 mm
Çap Dmax(S)	55,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00585

**Teknik veriler**

Meme ucu ailesi	N 018
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Çekme kuvveti	96,00 N
Emme kuvveti (-600mbar)	28,52 N
Ağırlık	22,90 g
Cilt	37,587 cm ³
Boyut	52,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Sipariş Verisi Aksesuarlar 10.01.06.00585**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440

