




FG 5 NBR-55 N017

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	5.00
Körük Sayısı	2.5



Tasarım verileri FG 5 NBR-55 N017

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	14.00 mm
Dış çap D1	6.0 mm
Kafa çapı Dk	7.0 mm
d2	2.6 mm
İç çap d	3.50 mm
Yay stroku Z	2.0 mm
Çap Ds	5.0 mm
Çap Dmax(S)	6.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00640

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 017
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	2.0 mm
Çekme kuvveti	0.80 N
Emme kuvveti (-600mbar)	0.32 N
Ağırlık	0.4 g
Boyut	5.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00640

**Veri aksesuarları sipariş edin 10.01.06.00640**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N017 M5-AG DN200 10.01.06.00314
Vantuz bağlantı nipel	SA-NIP N017 M5-IG DN200 10.01.06.00313

