


Art.-Nr.: 10.01.06.01106



FG-X 34 SI-30 N046

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	30,0 Shore A
размер	34,00
Количество складок	2,5



Конструктивные данные FG-X 34 SI-30 N046

Конструктивные данные

Attribute	Value
Высота H2	12,00 mm
Высота H	78,00 mm
Наружный диаметр D1	41,5 mm
Диаметр головки Dk	16,0 mm
d2	13,5 mm
Внутренний диаметр d	6,00 mm
Ход пружины Z	42,5 mm
Диаметр Ds	32,0 mm
Диаметр Dmax(S)	45,0 mm

Art.-Nr.: 10.01.06.01106



Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	30,0 Shore A
размер	34,00
Количество складок	2,5

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01106

