


Art.-Nr.: 10.01.06.01106



FG-X 34 SI-30 N046

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	30.0 Shore A
Size	34.00
Number of folds	2.5



Design data FG-X 34 SI-30 N046

Design data

Attribute	Value
Height H2	12.00 mm
Height H	78.00 mm
Outside diameter D1	41.5 mm
Head diameter Dk	16.0 mm
d2	13.5 mm
Internal diameter d	6.00 mm
Spring stroke Z	42.5 mm
Diameter Ds	32.0 mm
Diameter Dmax(S)	45.0 mm

Art.-Nr.: 10.01.06.01106

**Technical data**

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	30.0 Shore A
Size	34.00
Number of folds	2.5

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01106

**Ordering Data Accessories 10.01.06.01106**

Typ	Item number
Suction cup connection nipple	SA-NIP N046 G1/8-AG DN250
	10.01.06.03608

