

FGB-R 52x25 SI-50

Teknik veriler


Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50.0 Shore A
Boyutlar (LxW)	52 x 25
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Uzunluk L1	52.00 mm
Genişlik B1	25.00 mm
Yükseklik H	26.00 mm
Yay stroku Z	15.0 mm
Uzunluk L3	40.00 mm
Genişlik B3	13.00 mm
Vantuz genişliği Bs	25.00 mm
Ls	52.00 mm
Lmaks.(S)	54.50 mm
Bmaks(S)	27.50 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları Belirtilen strok, her katta bir destek çerçevesi ile kullanım içindir

Tasarım verileri FGB-R 52x25 SI-50



Körüklü vantuz (rekt.)

FGB-R 52x25 SI-50



Art.-Nr.: 10.01.06.01116



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50.0 Shore A
İş parçası yarıçapı dak (dışbükey)	10.0 mm
Emme kuvveti (-600mbar)	20.00 N
Ağırlık	8.0 g
Boyutlar (LxW)	52 x 25
Cilt	16.000 cm ³
Körük Sayısı	2.5
Ürün ailesi	FGB-R

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01116



WWW.SCHMALZ.COM/10.01.06.01116