

Körüklü vantuz (rekt.)

FGB-R 60x29 NBR-50



Art.-Nr.: 10.01.06.01117



FGB-R 60x29 NBR-50

Teknik veriler


Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	50.0 Shore A
Boyutlar (LxW)	60 x 29
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Uzunluk L1	60.00 mm
Genişlik B1	29.00 mm
Yükseklik H	26.00 mm
Yay stroku Z	14.0 mm
Uzunluk L3	48.00 mm
Genişlik B3	17.00 mm
Vantuz genişliği Bs	29.00 mm
Ls	60.00 mm
Lmaks.(S)	63.00 mm
Bmaks(S)	32.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları Belirtilen strok, her katta bir destek çerçevesi ile kullanım içindir

Tasarım verileri FGB-R 60x29 NBR-50



WWW.SCHMALZ.COM/10.01.06.01117

Körüklü vantuz (rekt.)

FGB-R 60x29 NBR-50



Art.-Nr.: 10.01.06.01117



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	50.0 Shore A
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Emme kuvveti (-600mbar)	36.00 N
Ağırlık	12.0 g
Boyutlar (LxW)	60 x 29
Cilt	22.000 cm ³
Körük Sayısı	2.5
Ürün ailesi	FGB-R

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01117



WWW.SCHMALZ.COM/10.01.06.01117