

Art.-Nr.: 10.01.06.01666




FSGA 33 NK-45 G1/4-AG DR

Sızdırmazlık halkalı körüklü vantuz, çeşitli çaplarda mevcuttur, sızdırmazlık halkası yapıştırılmış olarak teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	33.00
Körük Sayısı	1.5
Bağlantı	G1/4"-M
Meme ucu malzemesi	Alüminyum



Tasarım verileri FSGA 33 NK-45 G1/4-AG DR

Tasarım verileri

Attribute	Value
Yükseklik H	31.00 mm
Nominal çap dn	4.40 mm
d2	16.0 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	11.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	9.0 mm
Çap Ds	16.0 mm
Çap Dmax(S)	38.0 mm

Art.-Nr.: 10.01.06.01666



Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45.0 Shore A
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Ağırlık	15.6 g
Boyut	33.00
Körük Sayısı	1.5
Ürün ailesi	FSGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01666

