

Art.-Nr.: 10.01.06.01668



FSGA 33 NK-45 G1/4-IG DR


Sızdırmazlık halkalı körüklü vantuz, çeşitli çaplarda mevcuttur, sızdırmazlık halkası yapıştırılmış olarak teslim edilir.

## Teknik veriler

| Attribute                  | Value           |
|----------------------------|-----------------|
| Vantuz malzemesi           | Doğal Kauçuk NK |
| Malzeme sertliği [Shore A] | 45.0 Shore A    |
| Boyut                      | 33.00           |
| Körük Sayısı               | 1.5             |
| Bağlantı                   | G1/4"-F         |
| Meme ucu malzemesi         | Alüminyum       |

## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 46.60 mm |
| Nominal çap dn     | 4.40 mm  |
| d2                 | 16.0 mm  |
| Diş G1             | G1/4"-F  |
| Diş uzunluğu LG1   | 12.0 mm  |
| Anahtar boyutu SW1 | 17.0 mm  |
| Yay stroku Z       | 9.0 mm   |
| Çap Ds             | 16.0 mm  |
| Çap Dmax(S)        | 38.0 mm  |



Tasarım verileri FSGA 33 NK-45 G1/4-IG DR

Art.-Nr.: 10.01.06.01668



## Teknik veriler

| Attribute                  | Value           |
|----------------------------|-----------------|
| Vantuz malzemesi           | Doğal Kauçuk NK |
| Malzeme sertliği [Shore A] | 45.0 Shore A    |
| Ağırlık                    | 15.7 g          |
| Boyut                      | 33.00           |
| Körük Sayısı               | 1.5             |
| Ürün ailesi                | FSGA            |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



## Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.01668](http://www.schmalz.com/10.01.06.01668)

