

Art.-Nr.: 10.01.06.01668




FSGA 33 NK-45 G1/4-IG DR

Сифонная присоска с уплотнительным кольцом; для различных диаметров; поставляется с приклеенным уплотнительным кольцом.

Технические данные

Attribute	Value
Материал присоски	Натуральная резина НК
Твердость материала [Shore A]	45,0 Shore A
размер	33,00
Количество складок	1,5
Соединение	G1/4"-F
Материал ниппеля	алюминий



Конструктивные данные FSGA 33 NK-45 G1/4-IG DR

Конструктивные данные

Attribute	Value
Высота H	46,60 mm
Номинальный диаметр dn	4,40 mm
d2	16,0 mm
Резьба G1	G1/4"-F
Длина резьбы LG1	12,0 mm
Размер гаечного ключа SW1	17,0 mm
Ход пружины Z	9,0 mm
Диаметр Ds	16,0 mm
Диаметр Dmax(S)	38,0 mm

Art.-Nr.: 10.01.06.01668



Технические данные

Attribute	Value
Материал присоски	Натуральная резина НК
Твердость материала [Shore A]	45,0 Shore A
Вес	15,7 g
размер	33,00
Количество складок	1,5
Семейство продуктов	FSGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01668



WWW.SCHMALZ.COM/10.01.06.01668