



DR 46/36x5 S05 EPDM-15 KE

Технические данные

Attribute	Value
Твердость материала [Shore A]	15,0 Shore A
Материал уплотнения	EPDM
Функция вакуумного захвата большой площади	Клейкая лента с одной стороны
Тип материала	Губка S, высота 5 мм
Высота H	5,00 mm
Наружный диаметр D	46,00 mm
Внутренний диаметр d	36,00 mm

Конструктивные данные

Attribute	Value
Длина L	5,00 mm
Высота H	5,00 mm
Наружный диаметр D	46,00 mm
Внутренний диаметр d	36,00 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные DR 46/36x5 S05 EPDM-15 KE

**Технические данные**

Attribute	Value
Вес	0,5 g

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01678

