


Art.-Nr.: 10.01.06.01679



DR 28/21x3 C03 EPDM-15 KE

Технические данные

Attribute	Value
Твердость материала [Shore A]	15,0 Shore A
Материал уплотнения	EPDM
Функция вакуумного захвата большой площади	Клейкая лента с одной стороны
Тип материала	Губка C, Высота 3 мм
Высота H	3,00 mm
Наружный диаметр D	28,00 mm
Внутренний диаметр d	21,00 mm



Конструктивные данные DR 28/21x3 C03 EPDM-15 KE

Конструктивные данные

Attribute	Value
Длина L	3,00 mm
Высота H	3,00 mm
Наружный диаметр D	28,00 mm
Внутренний диаметр d	21,00 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

**Технические данные**

Attribute	Value
Вес	0,1 g

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Уплотнительное кольцо:

DR 28/21x3 C03 EPDM-15 KE



Art.-Nr.: 10.01.06.01679



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01679



WWW.SCHMALZ.COM/10.01.06.01679